



Pass and Seymour  
**PlugTail® 20A 125V Extra-Heavy Duty Hospital-Grade Power Indicating Duplex Receptacle, Red**  
Part No. PTTR8300PIRED



Built for the harshest medical environments, Pass and Seymour power indicating receptacles feature two industry-exclusive green LEDs that offer clear visual assurance of power indication at the receptacle even with critical equipment plugged into the device. The LEDs operate independently from one another to accommodate split-circuit wiring installations. Tamper-resistant protection comes standard with each receptacle to further enhance safety. For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

GE Lexan high impact-resistant lens.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Wire Size: #12 AWG THHN

## Specifications

### General Info

|                       |                |                   |                                    |
|-----------------------|----------------|-------------------|------------------------------------|
| Product Line          | Pass & Seymour | Color             | Red                                |
| Finish                | Matte          | Country Of Origin | Mexico                             |
| Number of Receptacles | 2              | Outlet Type       | Commercial, Indoor                 |
| Application Sector    | Hospital Grade | Standard          | CSA Listed, cULus, FSUL, UL Listed |
| Type                  | Outlet         |                   |                                    |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.625 in | Product Depth US | 0.866 in |
| Product Height US | 2.75 in  |                  |          |

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed                      Yes

---

## Technical Information

---

|                     |                          |                    |              |
|---------------------|--------------------------|--------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Temperature Rating | -40° - 60° C |
|---------------------|--------------------------|--------------------|--------------|

---

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

---

|           |        |                |        |
|-----------|--------|----------------|--------|
| Wire Size | 12 AWG | Indoor/Outdoor | Indoor |
|-----------|--------|----------------|--------|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---