



Wattstopper
Discontinued - PIR Multi-way Wall Switch Sensor w/nightlight Ivory
Part No. PW-103N-I



The PW-103N passive infrared (PIR) multi-way wall switch sensor can turn lights OFF and ON based on occupancy. It provides high sensitivity to small and large movements, appealing aesthetics, a field selectable nightlight and a variety of features.

Features & Benefits

Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI	Defaults to Manual-ON operation for maximum energy savings
Vandal resistant lens combines precise coverage with durability	In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually; ideal for presentations
Choice of Manual-ON or Auto-ON operation	Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds
Selectable audible and/or visual alerts for impending shutoff	2-wire and 3-wire models available for applications with or without neutral wire
High sensitivity and dense coverage for exceptional performance	Color-matched lens and low profile for appealing design
Optional nightlight with choice of three colors and two light levels	Allows multi-way control from one of up to four control locations
Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience	

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	RS-150BA-N-I
Color	Ivory	UPC Number	754182928613
Country Of Origin	China	Features	IR (Infrared), Motion Sensor, Nightlight

Switch Type	Motion Sensor	Application Sector	Commercial
Warranty Type	5-Year		
Dimensions			
Product Width US	2.0 in	Product Weight US	0.35 lb
Product Volume US	27.6 cu in	Product Depth US	2.75 in
Product Height US	4.48 in		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Response Frequency	50/60 Hz	Sensor Type	Occupancy
Number of Buttons	1	Amperage	4.3 A
Indicator	LED Light	Wattage	1200 W
Sensing Range	Minor motion 20 x 15 ft, Major motion 35 x 30 ft	Voltage	120/277 V
Connection Type	Wired		