



Pass and Seymour

**PlugTail® 20A 125V Hospital-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Gray**

Part No. PTTR8300GRY



PlugTail® Tamper-Resistant Hospital Grade Duplex Receptacle, Back and Side Wire, 20A, 125V. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects

Brushed finish.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

|                   |                  |                       |                            |
|-------------------|------------------|-----------------------|----------------------------|
| Product Line      | Pass & Seymour   | Color                 | Gray                       |
| Finish            | Matte            | UPC Number            | 785007013412               |
| Country Of Origin | Mexico           | Number of Receptacles | 2                          |
| Outlet Type       | Tamper-Resistant | Application Sector    | Commercial, Hospital Grade |

|          |                 |      |        |
|----------|-----------------|------|--------|
| Standard | UL 498, FEDSPEC | Type | Outlet |
|----------|-----------------|------|--------|

Dimensions

|                  |        |                  |          |
|------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
|------------------|--------|------------------|----------|

|                   |          |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                     |     |          |      |
|---------------------|-----|----------|------|
| Is Tamper-Resistant | Yes | Amperage | 20 A |
|---------------------|-----|----------|------|

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
|-----------------|-------------|-----------|-------------|

|                |        |
|----------------|--------|
| Indoor/Outdoor | Indoor |
|----------------|--------|