



By detecting arc faults and ground faults and deenergizing the circuit, the radiant® Tamper-Resistant Hospital Grade Dual Function Duplex Self-Test AFCI/GFCI receptacle is designed to protect against electrical fires in hospital applications. This receptacle features an indicator light and accessible test and reset buttons that make trips easier to identify and resolve compared to AFCI breaker alternatives. Via a feed-thru wiring configuration, all outlets installed downstream are also protected. As a part of the radiant® Collection, it also features sleek, clean lines for a sophisticated look. Made for use with screwless Wall Plates from the Collection, sold separately.

## Features & Benefits

Specifically designed for healthcare environments, this outlet protects against fire caused by arc-fault and ground fault occurrences. Unlike breaker alternatives, users can more easily fix trips with a convenient reset button on the outlet.	Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
Test and reset buttons located on face of device at point of use, making it easier to fix trips directly on the device.	SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected
Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced	Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly
Auto-ground clip assures a positive ground to a metal box	Compliant with NEC AFCI & GFCI requirements
Easier installation than breakers; fits any wall box; no need to match brand of breaker box	Accepts #14-#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire
Feed-through protection	Patented SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected
Prevents line-load miswire—no power to the face or downstream receptacles if wired incorrectly	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Satin	UPC Number	785007271140
Country Of Origin	China	Material	ABS
Number of Receptacles	2	Features	Durable, Indicator Lights
Outlet Type	Hospital Grade, Tamper-Resistant	Application Sector	Healthcare
Wall Plate Included	Yes	Warranty Type	1-Year Limited Warranty
Type	AFCI, Duplex, GFCI, Tamper-Resistant		

---

## Dimensions

---

Product Width US	1.74 in	Product Depth US	1.367 in
Product Height US	4.19 in	Product Length US	4.19 in

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

RoHS Compliant	Yes	Energy Savings	No
----------------	-----	----------------	----

---

## Technical Information

---

Is Tamper-Resistant	Yes	Connection Location	Back and Side
---------------------	-----	---------------------	---------------

---

Terminal Accommodation	#14 AWG - #10 AWG	Trip Range	5±1 mA
------------------------	-------------------	------------	--------

---

Number of Wires	3	Number of Gangs	1
-----------------	---	-----------------	---

---

Amperage	20 A	Number of Poles	2 Pole
----------	------	-----------------	--------

---

Is Weather Resistant	No	Indoor/Outdoor	Indoor
----------------------	----	----------------	--------

---

NEMA Configuration Code	5-20R	Mounting Type	Box
-------------------------	-------	---------------	-----

---

Wire Connection Type	Screw Terminal	Voltage	125.0 V
----------------------	----------------	---------	---------

---