



radiant Collection  
radiant® LED DIMMER 250W SP/3W W  
Part No. RHL373PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED 2-wire bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Designed to save energy, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating\* required for 2-gang applications. \*Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                    |                                   |                    |  |
|--------------------|-----------------------------------|--------------------|--|
| Product Line       | Pass & Seymour                    | Color              | White  |
| Finish             | Matte                             | UPC Number         | 785007161939   |
| Country Of Origin  | China                             | Features           | Color Change Kit, High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range) |
| Switch Type        | Paddle, Single Pole 3-Way, Slider | Number of Switches | 1  |
| Application Sector | Residential                       | Warranty Type      | Limited Lifetime Warranty  |
| Type               | Dimmer                            |                    |  |

Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.29 in | Product Depth US | 1.0 in |
| Product Height US | 3.18 in |                  |        |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|                       |                   |                      |   |
|-----------------------|-------------------|----------------------|---|
| Preset                | Yes               | Load Rating          | 120V 2.1A 250W (CFL), 120V 2.1A 250W (LED), 120V 300W (Halogen), 120V 300W (Incandescent) |
| Dimming Compatibility | Forward Phase     | Frequency Rating     | 60 Hz   |
| Number of Poles       | Single Pole 3-Way | Wire Size            | #14 - #10 AWG   |
| Requires Neutral Wire | No                | Indoor/Outdoor       | Indoor  |
| Mounting Type         | Wall Box          | Wire Connection Type | Screw Terminals   |
| Voltage               | 120 VAC           | Load Type            | CFL, Halogen, Incandescent, LED   |