

This Cisco® QSFP-100G-SR4-S Compatible QSFP28 transceiver provides 100GBase-SR throughput up to 100m over multi-mode fiber (MMF) at a wavelength of 850nm using a M... guaranteed to be 100% compatible with the equivalent Cisco® transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-tr... tested to ensure that it will initialize and perform identically. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. All Leg... Trade Agreements Act (TAA) compliant.

Features & Benefits

Distance Ranging from 100M to 40km (with FEC)	QSFP28 MSA Compliant
Dual Rate Operation of 103 and 112Gbps	IEEE 802.3ba LWDM Wavelengths
Includes Digital Optical Monitoring (DOM)	Commercial Temperature Range
TAA & BAA Compliant	1270nm to 1330nm wavelength signaling

Specifications

General Info			
Product Line	Legrand	UPC Number	757120667384
Country Of Origin	United States		