



Pass and Seymour  
2-Gang 302/304 Stainless Steel Wall Plate, Right of Center Power Outlet Receptacle 2.1563-in Diameter Opening  
Part No. SS705



2-Gang Power Outlet Receptacle Opening, 2.1563 in hole for 2.125-inch diameter device - 4 mtg. holes, Smooth 302/304 Metal.

## Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.

Variety of special plated finishes.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Brushed finish.

Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Packaged in protective film, with finish-matching screws.

Paintable to match plastic plates.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Stainless Steel
Finish	Metallic	UPC Number	785007136180
Country Of Origin	United States	Wall Plate Size	Standard Size
Wall Plate Type	Outlet, Round	Application Sector	Commercial, Residential
Standard	CSA	Warranty Type	1-Year Limited Warranty
Type	Wall Plate		

### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in	Circular Outlet Diameter	2.1563 mm

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Thickness	0.032 in	Number of Gangs	2
Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Orientation	Vertical		