



radiant Collection
radiant® 2-Wire Fluorescent Dimmer, White
Part No. RHFB83PW



Upgrade your space with precise dimming and exceptional style. This dimmer is designed for use with 2-wire fluorescent fixtures, and features the clean lines and smooth control of the radiant® Collection. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any basic switch or dimmer with ease, in both single-pole and 3-way applications. For use with 2-wire fluorescent lighting fixtures.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

No derating* required for 2-gang applications. *Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Constant memory features returns lights to their previous level after a power failure or outage.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Switch Type	Paddle
Number of Switches	1	Application Sector	Residential
Standard	CSA Listed, cULus, UL Listed	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Dimensions

Product Width US	2.5 in	Product Depth US	1.25 in
------------------	--------	------------------	---------

Product Height US 4.25 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Frequency Rating	120VAC 60 Hz	Connection	Screw Terminals
------------------	--------------	------------	-----------------

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Bulb Compatibility	Fluorescent	Number of Poles	3-Way, Single Pole
--------------------	-------------	-----------------	--------------------

Mounting Type	Box	Voltage	120 V
---------------	-----	---------	-------

Load	Fluorescent	Environmental Conditions	Humidity: Less than 95% non condensing
------	-------------	--------------------------	--
