



## Features & Benefits

Tough, impact-resistant thermoplastic housing.

Matches appearance of standard P&S toggle switch.

Uses conventional 3-way wiring when used in conjunction with a 3-way switch.

Specially designed capacitive circuitry to virtually eliminate fan motor "hum".

## Specifications

### General Info

|                   |                |                         |                        |
|-------------------|----------------|-------------------------|------------------------|
| Product Line      | Pass & Seymour | Replaced by Part Number | TSDDH163PLA            |
| Country Of Origin | China          | Application Sector      | Residential/Commercial |
| Standard          | cULus, RoHS    |                         |                        |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                          |  |            |                 |
|--------------------------|--|------------|-----------------|
| Frequency Rating         | 120VAC 60 Hz                           | Connection | Screw Terminals |
| Amperage                 | 1.6 A                                  | Voltage    | 120.0 V         |
| Environmental Conditions | Humidity: Less than 95% non condensing |            |                 |