

Specification Grade, Double-Throw, Maintained Contact Switch, 15A, 120 volts.



Features & Benefits

| | |
|--|--|
| Impact-resistant face and body. | Fully rounded back body protects wires from being damaged by sharp edges. |
| Clear identification of circuits. | External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG. |
| Ground screw position under the end of the strap minimizes the risk of contact. | Full wraparound metal strap with lock-in tabs. |
| Patented split circuit tab -- easily accessible, and can be reinstalled without a tool. | Unique "Up/Down" switches match the look and feel of standard Decorator switches. |
| Largest breadth of 15 amp offering. | All screws are tri-drive. |
| Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | China | Application Sector | Residential/Commercial |
| Standard | UL 20 | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | |
|----------|------|
| Amperage | 15 A |
|----------|------|
