



Pass and Seymour
Spec Grade Decorator Maintained Contact Switch, Ivory
Part No. TM811DTMAI



Specification Grade, Double-Throw, Maintained Contact Switch, 15A, 120 volts.

Features & Benefits

| | |
|--|--|
| Impact-resistant face and body. | Fully rounded back body protects wires from being damaged by sharp edges. |
| Clear identification of circuits. | External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG. |
| Ground screw position under the end of the strap minimizes the risk of contact. | Full wraparound metal strap with lock-in tabs. |
| Patented split circuit tab -- easily accessible, and can be reinstalled without a tool. | Unique "Up/Down" switches match the look and feel of standard Decorator switches. |
| Largest breadth of 15 amp offering. | All screws are tri-drive. |
| Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

| | | | |
|--------------------|-------------------------|---------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Satin | UPC Number | 785007157604 |
| Country Of Origin | China | Features | Decorator Style |
| Switch Type | Paddle | Number of Switches | 2 |
| Application Sector | Commercial, Residential | Wall Plate Included | No |
| Standard | UL 20 | Warranty Type | 1-Year Limited Warranty |

| | |
|------|--------------------------------|
| Type | Combination, Decorator, Switch |
|------|--------------------------------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------------|---|-----------------------|-----------|
| Load Rating | 15 A @ 120 VAC | Connection Location | Side Only |
| Terminal Accommodation | #14 AWG - #12 AWG | Number of Gangs | 1 |
| Throw Type | Double Throw | Amperage | 15 A |
| Number of Poles | Single Pole | Requires Neutral Wire | Yes |
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
| Wire Connection Type | Screw Terminals | Voltage | 120.0 V |
| Load Type | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon | | |