



radiant Collection
radiant® 15A Single-Pole Switch, White
Part No. TM870WCC10



The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant® Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard switch with ease, in as little as 10 minutes

Uses a paddle switch for smoother control with a low-profile aesthetic

Features durable, high-impact resistant thermoplastic construction

Designed to install easily with a narrower back body and captivated mounting screws

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection

Specifications

General Info

| | | | |
|--------------------|-------------------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | China | Switch Type | Paddle |
| Number of Switches | 1 | Application Sector | Residential/Commercial |
| Warranty Type | 1-Year Limited Warranty | Type | Switch |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 1.43 in | Product Depth US | 1.27 in |
| Product Height US | 4.19 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Gangs | 1 | Amperage | 15 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|-------------|---------------|-----|
| Number of Poles | Single Pole | Mounting Type | Box |
|-----------------|-------------|---------------|-----|

| | |
|---------|-----------|
| Voltage | 120/277 V |
|---------|-----------|
