



Pass and Seymour
15A 125V Commercial Grade Tamper-Resistant Duplex Receptacle, Light Almond
Part No. TR15LA



Tamper-Resistant Commercial Grade Receptacle, 15A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects. Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. Backed-out tri-drive steel terminal screws. Side wire only.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007241693
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.37 in	Product Depth US	0.93 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 1500V minimum	Is Tamper-Resistant	Yes
Connection	Side Wire	Number of Wires	3
Temperature Rating	-40° - 50° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Environmental Conditions	Flammability: UL94 V2