




Wiremold 5' Plugmold Multioutlet System with USB-C and USB-A, Stainless Steel Part No. S20GB509TRUAC



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). .040" (1.0 mm) steel housing. Packed two per carton. Each unit is supplied with one (1) Coupling and two (2) Blank End Fittings. USB-A is 2.4 Amps (shared between two ports) 5VDC. USB-C is 30W PD. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

Features & Benefits

USB charging: Single-port USB-C 30W PD & Dual-port USB-A charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

Compact design: Low-profile design installs in tight locations while offering multiple power and USB-A & USB-C charging connections. Receptacle spacing accommodates bulky AC adapters.

Multiple colors and finishes: Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

Tamper-resistant receptacles: Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

Specifications

General Info

Product Line	Wiremold	Color	Stainless Steel
UPC Number	786776196528	Country Of Origin	United States
Number of Receptacles	3	Application Sector	Commercial, Residential
Type	Plugmold		

Dimensions

Product Width US	1.1 in	Product Weight US	3.17 lb
Product Depth US	0.75 in	Product Length US	1.1 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Amperage	15 A	Indoor/Outdoor	Indoor
----------	------	----------------	--------

Environmental Conditions	Dry interior locations
--------------------------	------------------------
