



Pass and Seymour  
**15A 125V Tamper-Resistant Duplex Receptacle with USB A/C Fast Charging Ports, Light Almond**  
Part No. TR15USBAC6LA



Combination Tamper-Resistant 15A Duplex Convenience Receptacles with two fast charging 6A USB ports Type A and C

## Features & Benefits

Protects children: patented shutter system helps prevent improper insertion of foreign objects

Meets National Electrical Code® Tamper Resistant requirement

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

High-impact-resistant thermoplastic construction with tri-drive terminal screws

## Specifications

### General Info

|                       |   |                   |                                |
|-----------------------|---|-------------------|--------------------------------|
| Product Line          | Pass & Seymour  | Country Of Origin | China                          |
| Number of Receptacles | 2   | Features          | USB-A Charging, USB-C Charging |
| Outlet Type           | Commercial, Indoor, Residential, Tamper-Resistant, USB-Charging | Type              | Outlet                         |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.693 in | Product Depth US | 1.425 in |
| Product Height US | 2.677 in |                  |          |

### Technical Information

|                     |        |                  |             |
|---------------------|--------|------------------|-------------|
| Is Tamper-Resistant | Yes    | USB Amperage     | 6 A         |
| Number of USBs      | 2      | USB Power Output | 15 W        |
| Amperage            | 15 A   | Number of Poles  | Double Pole |
| Indoor/Outdoor      | Indoor | Voltage          | 125.0 V     |