



Clarity 10G TracJack, ETL tested as part of 100-meter 10 Gig channel solution. Front-loading and front removable. Universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned with synchronized reactance to Clarity 10G patch cords for optimum performance with minimized internal and alien crosstalk.

## Features & Benefits

Recessed design: Provides a more flush aesthetic look.

Meets Category 6A component standard: Ensures standards compliance.

Center tuned synchronized reactance design: Transparent interface with Clarity 10G cords.

Easy lace IDC housing: Reduces wiring time.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Front removable: Less intrusive access for adds, moves, changes

Standard TracJack footprint: Fits in all TracJack faceplates and housings.

Icon compatible, 10G Marking on jack face: Supports 606 designation requirements.

## Specifications

### General Info

|                    |                        |                   |             |
|--------------------|------------------------|-------------------|-------------|
| Product Line       | Ortronics              | Color             | Green       |
| UPC Number         | 662875620792           | Country Of Origin | Mexico      |
| Application Sector | Commercial, Industrial | Standard          | UL Standard |
| Warranty Type      | 5-Year                 | Type              | Jack        |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 0.73 in | Product Depth US | 1.1 in |
| Product Height US | 0.92 in |                  |        |

---

## Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

## Technical Information

---

|                |        |                   |         |
|----------------|--------|-------------------|---------|
| Wire Gauge     | 22 AWG | Termination Style | 110     |
| Connector Type | RJ-45  | Impedance         | 100 Ohm |

---