



Tamper-Resistant Spec Grade Receptacles, Back and Side-Wire, 15A, 125A

## Features & Benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground. For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial     | Standard          | UL 498 |

### Dimensions

---

|                  |          |                  |        |
|------------------|----------|------------------|--------|
| Product Width US | 1.625 in | Product Depth US | 0.9 in |
|------------------|----------|------------------|--------|

---

|                   |         |
|-------------------|---------|
| Product Height US | 2.75 in |
|-------------------|---------|

---

### Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

### Technical Information

---

|                     |     |       |   |
|---------------------|-----|-------|---|
| Is Tamper-Resistant | Yes | Phase | 3 |
|---------------------|-----|-------|---|

---

|                 |   |          |      |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 15 A |
|-----------------|---|----------|------|

---

|                 |             |           |             |
|-----------------|-------------|-----------|-------------|
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
|-----------------|-------------|-----------|-------------|

---

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|

---