



Tamper-Resistant Heavy-Duty Decorator Spec Grade Receptacles, Back and Side-Wire, 15A, 125A



## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial     | Standard          | UL 498 |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

---

|                     |             |           |             |
|---------------------|-------------|-----------|-------------|
| Is Tamper-Resistant | Yes         | Phase     | 3           |
| Number of Wires     | 3           | Amperage  | 15 A        |
| Number of Poles     | Double Pole | Wire Size | 14 - 10 AWG |
| Voltage             | 125.0 V     |           |             |

---