



Pass and Seymour

15A 125V Construction Spec-Grade Tamper-Resistant Single Receptacle, Back and Side Wire, Brown

Part No. TR5251

Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 15A, 125V



Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.	Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
.032 inch thick brass triple-wipe power contacts for lasting retention.	Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
Auto-ground clip assures positive ground.	Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007241990	Country Of Origin	Mexico
Number of Receptacles	1	Outlet Type	Tamper-Resistant

Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet
Dimensions			
Product Width US	1.38 in	Product Depth US	1.19 in
Product Height US	3.28 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Connection	Back and side wire	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Environmental Conditions	Flammability: UL94 V2