



Pass and Seymour
Tamper-Resistant Isolated Ground Hospital Grade Receptacle, Back and Side Wire, 15A, 125V, Gray
Part No. TRIG8200GRY



Tamper-Resistant Isolated Ground Hospital Grade Duplex Receptacle, Back and Side Wire, 15amp 125volt, Orange.For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

| | |
|--|---|
| Dual mechanical shutter system to help prevent insertion of foreign objects. | Auto-ground clip assures positive ground. |
| Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. | Backed-out tri-drive brass terminal screws for faster installation. |
| Internal screw-pressure-plate back and side wire capability. | Two back wire holes for additional wiring flexibility. |
| Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly. | .032 inch thick brass triple-wipe power contacts. |
| Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest. | For covering patents, see www.legrand.us/patents . |
| For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here. | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|----------------------|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007011999 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | cULus UL498, FEDSPEC |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.187 in | Product Depth US | 1.25 in |
| Product Height US | 2.625 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|--------------------------|--------------------------|---------------------|-------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Connection | Back and side wire | Number of Wires | 3 |
| Temperature Rating | -40° - 60° C | Amperage | 15 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
| Environmental Conditions | Flammability: UL94 V2 | | |