



Pass and Seymour

20A 125V Construction Spec-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Light Almond

Part No. TR5362LA



Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007243765
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	1.13 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor		