



Wiremold  
Plug-In Outlet Center Unit / 120V/15A/4 individually switched O/L /15' cord  
Part No. UL215BD



Four individually switched outlets, lighted on/off switch, rugged gray aluminum housing, 15A. 15' (4.6m) 14/3 SJT black cord with NEMA5-15 plug. Length 13" (330mm), width 2" (51mm). Receptacle center-to-center 2 1/8" (54mm). Snap-on, slide-off mounting.

## Features & Benefits

Four individually switched outlets, lighted on/off switch, rugged gray aluminum housing, 15A. 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 13" (330mm), width 2" (51mm). Receptacle center-to-center 2 1/8" (54mm). Snap-on, slide-off mounting.

## Specifications

### General Info

Product Line	Wiremold	Color	Aluminum, Gray
UPC Number	786776100921	Country Of Origin	Mexico
Material	Aluminum	Product Series	Plug-In Outlet Center
Receptacle Type	Simplex	Number of Receptacles	4
Features	Lighted Switch, Resettable Circuit Breaker	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

### Dimensions

Product Width US	2.0 in	Product Weight US	2.75 lb
------------------	--------	-------------------	---------

---

Product Depth US	1.89 in	Product Length US	12.25 in
------------------	---------	-------------------	----------

---

Receptacle Spacing	2.13 in
--------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Phase	Single	Cord Length	15 ft
-------	--------	-------------	-------

---

Amperage	15 A	Enclosure Type	Aluminum
----------	------	----------------	----------

---

Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
----------------	--------	---------------	------------

---

NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Slide-off, Snap-on
-------------------------	--------------	---------------	--------------------

---

Location Rating	Dry	Voltage	125.0 V
-----------------	-----	---------	---------

---

Environmental Conditions	Dry interior locations
--------------------------	------------------------

---