



**Wiremold**  
**Plug-In Outlet Center Unit / 120V/15A/48 long/16 O/L /lighted switch/6' cord**  
Part No. UL402BC



Sixteen outlets, lighted switch, rugged gray aluminum housing, 15A, 6' (1.8m) 14/3 SJT black cord with NEMA5-15 plug. Length 48" (1.2m). Receptacle center-to-center 2 1/2" (64mm). Snap-on, slide-off mounting.

## Features & Benefits

Sixteen outlets, lighted switch, rugged gray aluminum housing  
Length 48" (1.2m)  
Snap-on, slide-off mounting

15A, 14/3 SJT black cord with NEMA5-15 plug  
Receptacle center-to-center 2 1/2" (64mm)

## Specifications

### General Info

Product Line	Wiremold	Color	Aluminum, Gray
UPC Number	786776047776	Country Of Origin	Mexico
Material	Aluminum	Product Series	Plug-In Outlet Center
Receptacle Type	Simplex	Number of Receptacles	16
Features	Lighted Switch, Resettable Circuit Breaker	Application Sector	Commercial, Residential
Standard	cULus Recognized: File E66421 Guide XBYS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

### Dimensions

Product Width US	1.5 in	Product Weight US	3.7 lb
------------------	--------	-------------------	--------

---

Product Length US	48.0 in	Receptacle Spacing	2.5 in
-------------------	---------	--------------------	--------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Trade Programs

---

USMCA	Yes
-------	-----

---

### Technical Information

---

Phase	Single	Cord Length	6 ft
-------	--------	-------------	------

---

---

Amperage	15 A	Enclosure Type	Aluminum
----------	------	----------------	----------

---

---

Indoor/Outdoor	Indoor	Wiring Method	Cord-ended
----------------	--------	---------------	------------

---

---

NEMA Configuration Code	5-15P, 5-15R	Mounting Type	Snap-on, Slide-off
-------------------------	--------------	---------------	--------------------

---

---

Location Rating	Dry	Voltage	125.0 V
-----------------	-----	---------	---------

---

---

Environmental Conditions	Dry interior locations
--------------------------	------------------------

---