



## Wiremold 5' Plugmold Multioutlet System with USB-C and USB-A, Ivory Part No. V20GB509TRUAC



Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral, and insulated ground conductor). .040" (1.0 mm) steel housing. Packed two per carton. Each unit is supplied with one (1) Coupling and two (2) Blank End Fittings. USB-A is 2.4 Amps (shared between two ports) 5VDC. USB-C is 30W PD. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

### Features & Benefits

**USB charging:** Single-port USB-C 30W PD & Dual-port USB-A charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.

**Compact design:** Low-profile design installs in tight locations while offering multiple power and USB-A & USB-C charging connections. Receptacle spacing accommodates bulky AC adapters.

**Multiple colors and finishes:** Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.

**Tamper-resistant receptacles:** Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

### Specifications

#### General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776196535	Country Of Origin	United States
Number of Receptacles	3	Application Sector	Commercial, Residential
Type	Plugmold		

#### Dimensions

Product Width US	1.3 in	Product Weight US	3.78 lb
Product Depth US	0.75 in	Product Length US	1.3 in

#### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Trade Programs

---

USMCA	Yes
-------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Amperage	15 A	Indoor/Outdoor	Indoor
----------	------	----------------	--------

---

Environmental Conditions	Dry interior locations
--------------------------	------------------------

---