



Tamper-Resistant Spec Grade Receptacles, Back and Side-Wire, 15A, 125A

Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.	Exclusive patented feature, circuit label on face allows permanent circuit identification.
Extra heavy-duty brass, one-piece mounting strap with integral ground.	One-piece, brass, triple-wipe power contacts for lasting retention.
Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.	Impact-resistant nylon face and back body.
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.	Two drive screws anchor strap to back body and face.
Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
Auto-ground clip assures positive ground.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007145229	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42, FEDSPEC

Dimensions

Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Connection	Back and side wire	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Environmental Conditions	Flammability: UL94 V2		