



Pass and Seymour
20A 125V Spec-Grade Tamper-Resistant Duplex Receptacle, Back and Side Wire, Gray
Part No. TR63GRY

Tamper-Resistant Spec Grade Receptacles, Back and Side Wire, 20A, 125V



Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Auto-ground clip assures positive ground.

Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body.

Two drive screws anchor strap to back body and face. Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection. Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007268034	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Tamper-Resistant
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42, FEDSPEC
Type	Outlet		

Dimensions

Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Connection	Back and side wire	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Environmental Conditions	Flammability: UL94 V2
