



Tamper-Resistant Hospital Grade Receptacles, Back and Side Wire, 20A, 125V



Features & Benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Extra heavy-duty brass, one-piece mounting strap with integral ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- AC receptacles available in 15 and 20 Amp, 125V

One-piece, nickel-plated: brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and back body.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|----------------------------------|-----------------------|----------------------------|
| Product Line | Pass & Seymour | Color | Red |
| Finish | Matte | UPC Number | 785007145267 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Tamper-Resistant | Application Sector | Commercial, Hospital Grade |
| Standard | UL498, CSA C22.2 No. 42, FEDSPEC | Type | Outlet |

Dimensions

| | | | |
|-------------------|----------|------------------|--------|
| Product Width US | 1.625 in | Product Depth US | 0.9 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|---------------------|-------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
| Indoor/Outdoor | Indoor | | |