



Pass and Seymour
Tamper-Resistant Isolated Ground Decorator Spec Grade Receptacle, Back and Side Wire, 15A, 125V, Orange
Part No. TRIG26262



Tamper-Resistant Isolated Ground Decorator Spec Grade Duplex Receptacle, Back and Side Wire, 15amp 125volt, Orange. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007012378	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cULus UL498, FEDSPEC

Dimensions

Product Width US	1.187 in	Product Depth US	1.25 in
Product Height US	3.625 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Connection	Back and side wire	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Environmental Conditions	Flammability: UL94 V2		