



Vantage InFusion Controller II -24V

Part No. IC-24-II



The 24V InFusion Controller II possesses the required processor speed, RAM, and flash memory to meet the demands for delay-free control of large, complex systems. These requirements include control precision (where commands are completed instantaneously), real time feedback, a highly scalable system architecture, and programming for individual system personalization. Most buildings incorporate a number of controlled subsystems, including lighting, shades, HVAC, and more. The InFusion Controller provides seamless integration of these subsystems, enhancing the entire control experience.

Features & Benefits

Ample processor speed, RAM, and flash memory	Remote programming and firmware updates through Design Center software
Automatic backups of complete configuration each week to Micro SD card	Email notification support for Yahoo, Gmail, Hotmail, and more
Plug-and-play design for tool-free replacement of older InFusion systems	5 RS232 ports and 2 RS485 ports
Ethernet enabled for connectivity, expansion, and integration	Scalable up to seven enclosures per controller
Tracks real and astronomical time	Up to 120 low-voltage or 38 Equinox 40 stations, 120 wireless stations

Specifications

General Info

Product Line	Vantage	UPC Number	804428068341
Country Of Origin	China	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Controller

Dimensions

Product Width US	7.88 in	Product Weight US	3.55 lb
Product Depth US	3.0 in	Product Height US	6.62 in

Listing Agencies / 3rd Party Agencies

CE Certified	Yes	cUL Listed	Yes
--------------	-----	------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Storage Humidity	5-95% RH (Non-Condensing)	Security	Password Protected
------------------	---------------------------	----------	--------------------

Frequency Range	50-60 Hz	Indoor/Outdoor	Indoor
-----------------	----------	----------------	--------

Wattage	200 W	Operating Temperature	0°-40°C, 32°-104°F
---------	-------	-----------------------	--------------------

Mounting	Enclosure Mounted	Voltage	120 to 277 V
----------	-------------------	---------	--------------
