



Pass and Seymour
20A 125V Heavy Duty Spec-Grade Tamper-Resistant Isolated Ground Duplex Receptacle, Ivory
Part No. TRIG5362I



Tamper-Resistant Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle, Back and Side Wire, 20A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Backed-out tri-drive brass terminal screws for faster installation.

Two back wire holes for additional wiring flexibility.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Internal screw-pressure-plate back and side wire capability.

.032 inch thick brass triple-wipe power contacts.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Application Sector	Commercial
Standard	cULus UL498	Type	Outlet

Dimensions

Product Width US	1.187 in	Product Depth US	1.25 in
------------------	----------	------------------	---------

Product Height US	2.625 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Connection	Back and side wire	Number of Wires	3
------------	--------------------	-----------------	---

Temperature Rating	-40° - 60° C	Amperage	15 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------
