



Wattstopper
Ultrasonic Ceiling Occupancy Sensor, 100-347VAC, 500 sq ft
Part No. UT-355-1



Wattstopper's low-profile UT-355 Ultrasonic Line Voltage Ceiling Sensor automatically turns lighting on and off based on occupancy. The sensor mounts on the ceiling with a flat, unobtrusive appearance and provides 360° coverage.

Features & Benefits

Architecturally appealing low-profile appearance

Utilizes advanced, omni-directional, ultrasonic technology

Ultrasonic diffusers provide more comprehensive coverage

Operates at 120, 230 (single phase), 277 or 347 VAC, 50/60 Hz

Terminal wiring for quick and easy installation

Walk-through mode increases savings potential

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182915200
Country Of Origin	China	Product Series	UT-355
Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Sensitivity Adjustment	Installation Location	Ceiling
Included	Mounting Screws	Application Sector	Commercial
Standard	UL, cUL, PEP	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.5 in	Product Weight US	0.337 lb
------------------	--------	-------------------	----------

Product Volume US	69.6 cu in	Product Depth US	1.9 in
Product Height US	4.5 in		
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	1200 W @ 230 VAC, 1200 W @ 277 VAC, 1500 W @ 347 VAC, 800 W @ 120 VAC	Ultrasonic Frequency	40 kHz
Has Battery	No	Sensor Coverage Pattern	360 deg
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	8-10 ft	Number of Buttons	0
Sensor Technology	Ultrasonic	Timer Duration	30 Seconds, 5-30 Minutes
Indicator	Ultrasonic Detection LED	Input Voltage	120/230/277/347 VAC
Line Frequency	60 Hz	Indoor/Outdoor	Indoor
Sensor Coverage	500 sq ft	Mounting Type	2-1/4 in Deep J-Box, Surface
On Function	Auto On	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	24 x 24 ft
Wire Connection Type	Screw Terminals	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		