



Wiremold Steel Divider Ceiling Panel

Part No. LCP-US-DIV

Divider designed for use with the Ceiling Panel system to separate power and data within a single compartment. Helps maintain organized service layouts while supporting flexible, future configuration changes.



Features & Benefits

Standardized & Fully Specifiable. Simplifies and streamlines design, bidding and approvals.

Faster Alternative to Custom Fabrication. A faster, simpler path than traditional shop-built solutions.

Ideal for healthcare, research facilities, commercial, education and quick service restaurant environments.

Integrated & Field-Configurable Services. Power, data and lab utilities like air, gas and vacuum in one panel.

Clean, Consistent Aesthetic. Delivers a uniform ceiling appearance with repeatable quality.

Designed for Change. Reconfigurable/updatable for changing needs.

Specifications

General Info

| | | | |
|--------------------|--|-------------------|--|
| Product Line | Wiremold | Color | Gray |
| UPC Number | 786776200843 | Country Of Origin | United States |
| Material | Steel | Construction | Sheet Metal |
| Application Sector | Commercial, Education, Healthcare, Healthcare, Hospitality, Industrial | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | Electrical Ceiling Panel | | |

Dimensions

| | | | |
|-------------------|--------|------------------|--------|
| Product Width US | 4.0 in | Product Depth US | 3.5 in |
| Product Length US | 4.0 in | | |

Trade Programs

| | | | |
|-------|-----|-----|-----|
| USMCA | Yes | BAA | Yes |
|-------|-----|-----|-----|

Additional Information

| | | | |
|----------------|-----|----------------|----|
| RoHS Compliant | Yes | Energy Savings | No |
|----------------|-----|----------------|----|

Technical Information

| | | | |
|----------------|----|---------------------|----|
| Seismic Tested | No | Is Tamper-Resistant | No |
|----------------|----|---------------------|----|

| | | | |
|--------------|----|----------|------|
| Is Pre-Wired | No | Amperage | 60 A |
|--------------|----|----------|------|

| | | | |
|----------------|--------|---------------|----------------|
| Indoor/Outdoor | Indoor | Mounting Type | Screw-on Mount |
|----------------|--------|---------------|----------------|

| | | | |
|-----------------|---|---------|---------|
| Number of Holes | 2 | Voltage | 600.0 V |
|-----------------|---|---------|---------|
