



Tamper-Resistant, Weather-Resistant Commercial Grade Receptacles, 20A, 125V



Features & Benefits

Auto-ground clip assures positive ground.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Heavy-duty, brass strap for added strength and ground conductivity.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Tri-drive brass terminal screws. Internal screw pressure plate back and side wire capability. Two back wire holes for more wiring flexibility.

Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007242553	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Tamper-Resistant, Weather-Resistant
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

Type	Outlet		
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 1500V minimum	Connection	Side Wire
Number of Wires	3	Temperature Rating	-40° - 50° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Outdoor
Environmental Conditions	Flammability: UL94 V2		