



Tamper-Resistant, Weather-Resistant Commercial Grade Receptacles, 20A, 125V



## Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Outdoor, Tamper-Resistant, Weather-Resistant	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

---

## Dimensions

---

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 1500V minimum	Connection	Side wire
Number of Wires	3	Temperature Rating	-40° - 50° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Outdoor
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2

---