



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 250V



Features & Benefits

| | |
|--|---|
| Auto-ground clip assures positive ground. | WR marking on face as required by UL Standard. |
| Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations. | Strap tabs wrap around face to prevent strap from separating from face and back body. |
| Tri-drive brass terminal screws. | Internal screw-pressure-plate back and side wire capability. |
| Two back wire holes for more wiring flexibility. | Heavy-duty, brass strap for added strength and ground conductivity. |
| UV-resistant nylon face for longer life under adverse environmental conditions. | Two drive screws anchor strap to back body and face where abrupt removal torque is strongest. |
| Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. | .032 inch thick brass triple-wipe power contacts for lasting retention. |
| For covering patents, see www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . |

Specifications

General Info

| | | | |
|-------------------|-----------------|--------------------|--------------|
| Product Line | Pass & Seymour | UPC Number | 785007243154 |
| Country Of Origin | United States | Application Sector | Commercial |
| Standard | UL 498, FEDSPEC | | |

Dimensions

| | | | |
|-------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

| | | | |
|-------|-------|-----------------|---|
| Phase | Three | Number of Wires | 3 |
|-------|-------|-----------------|---|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|--|--|
| Wire Size | 14 - 10 AWG | | |
|-----------|-------------|--|--|