



# WATTSTOPPER

## POWER YOUR ENERGY EFFICIENCY PROGRAMS

with Wattstopper's Proven Lighting Controls

### GUIDE INFORMATION KEY START HERE

CONTROLS GUIDE IMPORTANT INFORMATION	
NO.	NOTE
1	Popular options shown. Additional models are available; see <a href="#">website</a> for details.
2	For additional product information, click the corresponding <i>Catalog #</i> to view the product page.
3	* US made option (# ends in"-U")
4	347V** version # ends in "-347" and may have limited color options

[Click here for a Printable Version](#)

CONTROLS GUIDE LEGEND				
APPLICATION KEY				
<b>CR</b>	<b>E</b>	<b>HS</b>	<b>BR</b>	
<b>OO</b>	<b>R</b>	<b>SO</b>	<b>SR</b>	

  

WHITE	IVORY	LIGHT ALMOND	GRAY
<b>W</b>	<b>I</b>	<b>LA</b>	<b>G / GRY</b>
BROWN	BLACK	RED	TRI-COLOR (White, Ivory, Light Almond)
<b>BR</b>	<b>B / BK</b>	<b>R</b>	<b>TC</b>

	CATALOG #	VOLTAGE	UNIQUE FEATURES	TECHNOLOGY	COVERAGE	APPLICATIONS								
						CR	E	HS	BR	OO	R	SO	SR	
	<a href="#">CB-100</a>	24VDC	Cold Location	PIR	2000 ft <sup>2</sup> , 90 - 120 ft linear	●								
	<a href="#">CI-300</a>	24VDC/AC	Low Profile, CI-300 has Isolated Relay and Light Level Sensor	PIR	500 - 1200 ft <sup>2</sup>	●		●						
	<a href="#">CI-305</a>													
	<a href="#">CX-100*</a>	24VDC/AC	Corner Mount, CX-100 has Isolated Relay and Light Level Sensor	PIR	300 - 2000 ft <sup>2</sup> , 90 - 120 ft linear	●		●	●	●	●	●	●	
	<a href="#">CX-105</a>													
	<a href="#">DT-200*</a>	24VDC/AC	Selectable Trigger Mode, DT-200 has Isolated Relay and Light Level Sensor	Dual Technology	2000 ft <sup>2</sup>	●		●	●	●	●	●	●	
	<a href="#">DT-205</a>													
	<a href="#">DT-300*</a>	24VDC/AC	Low Profile, Selectable Trigger Mode, 40kHz, 6 Occupancy Logic Options, DT-300 has Isolated Relay and Light Level Sensor	Dual Technology	1000 ft <sup>2</sup>	●		●	●	●	●	●	●	
	<a href="#">DT-305*</a>													
	<a href="#">DT-355*</a>	120V, 230V, 277V, 347V	Low-profile, Line Voltage, 40kHz, 6 Occupancy Logic Options, No Power Pack Required	Dual Technology	1000 ft <sup>2</sup>	●		●	●	●	●	●	●	
	<a href="#">UT-300</a>	24VDC/AC	Low Profile, Configurable Zone Patterns, 40kHz, UT-300 has Isolated Relay	Ultrasonic	500 - 2000 ft <sup>2</sup>	●		●	●	●	●	●	●	
	<a href="#">UT-305</a>													
<a href="#">UT-355</a>	<a href="#">UT-355</a>	120V, 230V, 277V, 347V	Line Voltage, Low-profile, 40kHz, No Power Pack Required	Ultrasonic	500 - 2000 ft <sup>2</sup>	●		●	●	●	●	●	●	

	CATALOG #	VOLTAGE	UNIQUE FEATURES	NEUTRAL REQUIRED	APPLICATIONS		
					E	BR	OO
	<a href="#">LPB-8</a>	120V, 240V, 277V, 347V**	Scheduled Control for up to 8 Relays, Surface or Flush Mount Options, Optional Group Card	Y	●	●	●
	<a href="#">LPB-8</a>						
	<a href="#">LCB-120/277</a>	120V, 277V	Scheduled Control for up to 8 Relays, Accommodates Double-Pole (LCDP-1) and Dual, Single-Pole (LCS-2) Relay Modules (not included), Astronomical Time Clock	Y	●	●	●

	CATALOG #	VOLTAGE	UNIQUE FEATURES	TECHNOLOGY	COVERAGE
	<a href="#">HB3x0W</a>	120V, 240V, 277V, 347V, 24VDC	Line or Low Voltage, Mounting from 8-40' Options for Cold Locations (-40F to 131F, -40C to 55C), Wet Locations (IP65 rated), Optional Backbox	PIR	40-100 ft

	CATALOG #	UNIQUE FEATURES
	<a href="#">HBEM3</a>	Extender Module for Mounting on Side of the Fixture for HBxxx-B series

	CATALOG #	VOLTAGE	UNIQUE FEATURES	COLOR	TECHNOLOGY	APPLICATIONS			
						CR	BR	OO	SO
	<a href="#">WRC-15-1-W</a>	120V	15A Duplex Receptacle, Half or Full Control Options	W	Works with WRC-TX RF Transmitter	●	●	●	●
	<a href="#">WRC-15-2-W</a>								
	<a href="#">WRC-20-1-W</a>	120V	20A Duplex Receptacle, Half or Full Control Options	W	Works with WRC-TX RF Transmitter	●	●	●	●
	<a href="#">WRC-20-2-W</a>								
<a href="#">WRC-TX</a>	24VDC	RF Transmitter, Up to 16 WRC Receptacles	W	Works with any 24V Wattstopper Occupancy Sensor	●	●	●	●	

	CATALOG #	VOLTAGE	UNIQUE FEATURES
	<a href="#">BZ-150</a>	120V, 230V, 240V, 277V	Auto or Manual On/Off, Hold-On, Hold-Off, Input for Low Voltage Momentary Switch
	<a href="#">BZ-200</a>	120V-277VAC	Auto On, Rated for Lighting or Plug Loads; Load On/Off Button
	<a href="#">BZ-250</a>	120V-347V**	Auto or Manual On/Off, Rated for Lighting or Plug Loads; Load On/Off Button, Input for Low Voltage Momentary Switch
	<a href="#">B347D-P</a>	347V	Ballast Load, 150mA

	CATALOG #	VOLTAGE	UNIQUE FEATURES	COLOR	NEUTRAL REQUIRED	APPLICATIONS	
						E	SR
	<a href="#">RT-50</a>	120VAC	Preset 6 Button Countdown with On/Off Override	W	Y	●	●
	<a href="#">RT-200</a>	120V, 277V	Astronomical, Dawn/Dusk Scheduling, Optional Time Delay	W, I, LA, A, B	Y	●	●
	<a href="#">TS-400</a>	120V, 277V, 24VDC/AC (Part # ends in "-24")	Digital Countdown Timer	W, I, LA, G, B, R	N	●	●

	CATALOG #	VOLTAGE	UNIQUE FEATURES	COLOR	NEUTRAL REQUIRED
	<a href="#">RHH703PTU</a>	120V; 450W CFL/LED; 700W Incandescent, Halogen & ELV; 500VA MLV; 5.5A EFL	radiant* Tru Universal Single Pole/3-Way, Preset	W, TC	N
	<a href="#">RH4FBL3P</a>	120V 10A, 277V 5A	radiant* LED/Fluorescent Single Pole, Preset, 0-10V 4-wire	W, TC	N

	CATALOG #	VOLTAGE	UNIQUE FEATURES	COLOR
	<a href="#">DCLV2</a>	24VDC	0-10V Dimmer Manual-On or Automatic-On, Optional Input for 24VDC Occupancy Sensors	W, I, LA, G, B, R

	CATALOG #	VOLTAGE	UNIQUE FEATURES	COLOR	TECHNOLOGY	COVERAGE	NEUTRAL REQUIRED	APPLICATIONS					
								CR	HS	BR	R	SO	SR
	<a href="#">DSW-301*</a>	120V, 277V, 347V**	Light Level Sensor, Multi-Way, Selectable Trigger Mode	W, I, LA, G, B, R	Dual Technology	1050 ft <sup>2</sup>	Optional	●	●	●	●	●	●
	<a href="#">DSW-302*</a>	120V, 277V, 347V**	Dual Relay, Light Level Sensor, Multi-Way, Selectable Trigger Mode	W, I, LA, G, B, R	Dual Technology	1050 ft <sup>2</sup>	Optional	●	●	●	●	●	
	<a href="#">DW-311*</a>	120V, 277V, 347V**	0-10V Dimming, Partial-On Option, Light Level Sensor, Multi-Way, Selectable Trigger Mode	W, I, LA, G, B, R	Dual Technology	1050 ft <sup>2</sup>	Y	●	●	●	●	●	
	<a href="#">PW-100-24</a>	24VDC/AC	Light Level Sensor, Multi-Way, Requires Power Pack	W	PIR	1050 ft <sup>2</sup>	N	●	●	●	●	●	
	<a href="#">PW-101D</a>	120V	Light Level Sensor, Incandescent Magnetic Low Voltage, Electronic Low Voltage or 2-wire Fluorescent, Dimmer	W	PIR	1050 ft <sup>2</sup>	Y	●	●	●	●	●	
	<a href="#">PW-301*</a>	120V, 277V, 347V**	Light Level Sensor, Multi-Way	W, I, LA, G, B, R	PIR	1050 ft <sup>2</sup>	Optional	●	●	●	●	●	
	<a href="#">PW-302*</a>	120V, 277V	Dual Relay, Light Level Sensor, Multi-Way	W, I, LA, G, B, R	PIR	1050 ft <sup>2</sup>	Optional	●	●	●	●	●	
	<a href="#">PW-311*</a>	120V, 277V	0-10V Dimming, Partial-On Option, Light Level Sensor, Multi-Way	W, I, LA, G, B, R	PIR	1050 ft <sup>2</sup>	Optional	●	●	●	●	●	
	<a href="#">WS-301*</a>	120V, 277V	Light Level Sensor	W, I, LA, G, B, R	PIR	900 ft <sup>2</sup>	Optional	●	●	●	●	●	

	CATALOG #	VOLTAGE	UNIQUE FEATURES	TECHNOLOGY	COVERAGE	NEUTRAL REQUIRED	APPLICATIONS					
							CR	HS	BR	R	SO	SR
	<a href="#">CS-50-W</a>	120V	LED Status Indicator	PIR	600 ft <sup>2</sup>	N		●	●	●	●	●
	<a href="#">CS-350-N-W</a>	120V	Dual Relay, Nightlight	PIR	600 ft <sup>2</sup>	Y		●	●	●	●	●
	<a href="#">CU-250-W</a>	120V	Multi-Way	Ultrasonic	600 ft <sup>2</sup>	Y		●	●	●	●	●
	<a href="#">DSW-301M-W</a>	120V, 277V	Light Level Sensor, Multi-Way	Dual Technology	1050 ft <sup>2</sup>	Optional	●	●	●	●	●	●
	<a href="#">RS-150BA-N-W</a>	120V	Nightlight	PIR	600 ft <sup>2</sup>	Y		●	●	●	●	●

	CATALOG #	UNIQUE FEATURES	COLOR
	<a href="#">TP26</a>	1-4 Gang Options, Low-Profile	W, I, LA, GRY, RED, BR