



Wiremold  
V24GB506 Steel Plugmold® Multioutlet Strip  
Part No. V24GB506



5' Steel Plugmold Multioutlet Strip with 10 single receptacles spaced 6"

## Features & Benefits

|  |  |
|--|--|
| Steel Raceway. Provides superior strength for any dry location installation with greater wire capacity than V2000.         | Ivory ScuffCoat finish. Durable scratch resistant finish.  |
| Removable cover. Allows easy access to wiring for changes or additions.  | Full range of fittings. Provides a complete wiring solution.   |
| Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device. | Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 20A, 120V receptacles. Ideal for short runs requiring additional outlets in electrically busy areas. |
| Single or alternating circuit. Meets virtually any circuit requirement.  | Choice of receptacle spacing. Center spacing between receptacles of 6", 12" and 18".   |
| Simplex receptacle. More spacing options available.  | Duplex receptacle. Aesthetically pleasing, functional 20A duplex for the 24S (2400) Series.  |
| Customization available. All products can be modified to accommodate virtually any application.                            | This product meets the material restrictions of RoHS.  |

## Specifications

### General Info

|                   |               |                       |              |
|-------------------|---------------|-----------------------|--------------|
| Product Line      | Wiremold      | UPC Number            | 786776085419 |
| Country Of Origin | United States | Number of Receptacles | 10           |

|                                       |            |                          |  |
|---------------------------------------|------------|--------------------------|--|
| Application Sector                    | Commercial | Standard                 | cULus Listed Base & Blank Cover: File E4376 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E41751 Guide RJPR. Base & Blank Cover& Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC. |
| Type                                  | Plugmold   |                          |  |
| Dimensions                            |            |                          |  |
| Product Width US                      | 1.9 in     | Product Depth US         | 0.9 in   |
| Product Length US                     | 1.9 in     |                          |  |
| Listing Agencies / 3rd Party Agencies |            |                          |  |
| cULus ListingNumber                   | E15191     | cULus Listed             | Yes  |
| Buy American Act Compliance           |            |                          |  |
| NAFTA                                 | Yes        |                          |  |
| Additional Information                |            |                          |  |
| RoHS Conformant                       | Yes        |                          |  |
| Technical Information                 |            |                          |  |
| Amperage                              | 15 A       | Enclosure Type           | Steel  |
| Voltage                               | 125.0 V    | Environmental Conditions | Dry interior locations   |