



adorne Collection  
adorne® 15A Tamper-Resistant Dual-Controlled Outlet, White  
Part No. ARCD152W10



A modern upgrade for style, safety and energy management, this tamper-resistant, dual-controlled outlet from the adorne Collection installs easily in place of an existing outlet. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Independently cut power to either plug when not in use to conserve energy.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Finish	Matte
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Indoor, Residential, Tamper-Resistant	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty
Type	Outlet		

### Dimensions

Product Width US	1.77 in	Product Depth US	1.73 in
------------------	---------	------------------	---------

---

Product Height US 2.12 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

### Technical Information

---

Is Tamper-Resistant Yes

Phase

Single

---

Connection Side and Back Wire

Number of Wires

3

---

Number of Gangs 1

Amperage

15 A

---

Number of Poles Double Pole

Wire Size

14 - 10 AWG

---

Indoor/Outdoor Indoor

NEMA Configuration Code

5-15R

---

Mounting Type Box

Voltage

125.0 V

---

Connection Type Internal Pressure Plates

Environmental Conditions

95% (relative humidity, non-condensing)

---