

Turnlok® Connector 4-Wire 30A 125/250V



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scalloped shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Application Sector | Industrial |
| Standard | UL 498 | | |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 3.33 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|---|----------|------|
| Number of Wires | 3 | Amperage | 30 A |
|-----------------|---|----------|------|

| | | | |
|-----------------|-------------|-----------|---|
| Number of Poles | Double Pole | Wire Size | 4 |
|-----------------|-------------|-----------|---|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
