




Wiremold
4000 Radiused Full Capacity Divided Tee Fitting
Part No. V4015DFO



Full capacity, divided tee fitting. Provides 2" (51mm) cable bend radius for UTP, STP and fiber optic installations. Ideal for new installations whether the cable is lay-in or pull-through.

Features & Benefits

Full capacity, divided tee fitting. Provides 2" (51mm) cable bend radius for UTP, STP and fiber optic installations. Ideal for new installations whether the cable is lay-in or pull-through.

Specifications

General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776537048	Country Of Origin	United States
Product Series	4000 Series	Installation Location	On Wall
Application Sector	Commercial	Standard	cULus Listed Raceway: File E4376 Guide RJBT. Fittings: File E41751 Guide RJPR. Base & Blank Cover: Meets Article 386 of NEC. Meets Section 12- 600 of CEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Fitting

Dimensions

Product Weight US	3.43 lb	Product Depth US	1.75 in
-------------------	---------	------------------	---------

Product Length US	12.75 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E41751	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Is Pre-Wired	No	Indoor/Outdoor	Indoor
--------------	----	----------------	--------

Voltage	600.0 V
---------	---------