




Vantage Standard Dimming Module Retro Terminal Kit Part No. TROSDM-KIT



Vantage's AC Terminal Boards are sold and installed separately from the enclosures. This allows the installer to use different module models inside the enclosure. The TROSDM-KIT supports the SDM12-EM Module for retrofit installations in existing enclosures.

Features & Benefits

Terminal boards support eight loads as well as two line feeds and 12 neutrals.

For enclosures that pre-date the plastic standoffs (enclosures shipped before February 2005) and uses pem-studs (metal standoffs) instead, this kit is required.

Includes one TROSDM-L (4 load, left board), one TROSDM-R (4 load, right board), module load labels (one pair), two #6-32 x 7/8 Screws

Specifications

General Info

Product Line	Vantage	UPC Number	804428054078
Country Of Origin	China	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Terminal Board

Dimensions

Product Width US	2.125 in	Product Weight US	10.4 oz
Product Depth US	0.875 in	Product Height US	7.8 in

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----

Additional Information

Energy Savings	No
----------------	----

Technical Information

Compatibility	InFusion	Wire Gauge	10-14 AWG
---------------	----------	------------	-----------

Storage Humidity	5-95% RH (Non-Condensing)	Indoor/Outdoor	Indoor
------------------	---------------------------	----------------	--------

Operating Temperature	0°-40°C, 32°-104°F
-----------------------	--------------------
