



Straight Blade Connector 2-Pole 3-Wire 15A 250V

## Features & Benefits

Unit arrives completely ready-to-wire, cuts installation time significantly.

Nylon housing provides impact and chemical resistance.

Rugged two-piece cord grip provides more uniform cord retention.

Internal dust shield keeps terminals free of contaminants.

Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.

All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.

Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.

Cord-grip screws recessed to protect installer against screwdriver head slippage.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Black      |
| Country Of Origin | Mexico         | Application Sector | Industrial |
| Standard          | UL498          |                    |            |

### Dimensions

|                  |          |                   |          |
|------------------|----------|-------------------|----------|
| Product Width US | 1.516 in | Product Length US | 1.752 in |
|------------------|----------|-------------------|----------|

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

### Technical Information

---

|                 |             |           |            |
|-----------------|-------------|-----------|------------|
| Number of Wires | 3           | Amperage  | 15 A       |
| Number of Poles | Double Pole | Wire Size | 14 - 0 AWG |
| Voltage         | 250.0 V     |           |            |

---