



**Q-Series 1, 2 & 4 Panel Standard Density Wall Mount Fiber Enclosures**

The Q-Series Wall Mounted fiber enclosure system is designed to support standard density LAN or POL applications in building networks. The all steel chassis enables reliable protection and management of fiber optic cable patching, splicing, and connecting. The enclosure also enables distribution of backbone cabling to active equipment, switching, or cross/interconnect horizontal area. The 2 panel footprint accommodates up to 48 LC fibers, while the 4 panel accommodates up to 96 LC fibers. Each enclosure is compatible with OFP Adapter Panels, Compact 12 Fiber Splice Trays, and M2 Pre-terminated or Splice Cassettes.

**Features & Benefits**

**Standard Density**

Accepts 12 or 24 fiber M2 pre-terminated or splice cassettes, FST4-F012C splice tray, and OFP adapter panels

**Cable Management**

Protect and safely route all sensitive fibers with the included cable management system, central strength member bracket, and bend limiters

**Low-Profile Design**

Providing unobtrusive protection and management of all enclosed cabling infrastructure

**Cable Ingress and Egress**

Four ingress or egress points with rubber grommets help to protect and route all connectivity infrastructure.

**Specifications**

**General Info**

UPC Number	662875029199	Country Of Origin	China
Product Line	Legrand	Included	Rubber grommets, labels, cable management clips, cable cradle
Type	Enclosure		

**Technical Information**

Mounting	Wall	Compatibility	OFP/M2/LM2
Frame	Steel		