



Pass and Seymour

20A 125V Commercial Grade Tamper-Resistant Weather-Resistant Duplex Receptacle, Light Almond

Part No. WR20TRLA

Tamper-Resistant, Weather-Resistant Commercial Grade Receptacles, 20A, 125V



Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007242560
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant, Weather-Resistant	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 1500V minimum	Connection	Side Wire
Number of Wires	3	Temperature Rating	-40° - 50° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Outdoor
Environmental Conditions	Flammability: UL94 V2		