



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 125V



Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

UV-resistant nylon face for longer life under adverse environmental conditions.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

WR marking on face as required by UL Standard.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Internal screw-pressure-plate back and side wire capability.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	WR20TRGRY
Color	Gray	UPC Number	785007242522
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498, FEDSPEC		

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		