PASS & SEYMOUR®
Specification Grade Self-Test GFCIs
15 & 20A, 125VAC

1597, 2097, 1597NTLTR, 2097NTLTR, 1597TR, 2097TR, 1597TRWR, 2097TRWR, 1597TRA, 2097TRA, 1597IGTR, 2097IGTR, 1597SWTTR, 2097NA, 1597TRNA, 2097TRNA, 1597TRWRNA, 2097TRWRNA,1597TRSGL, 2097TRSGL, 1597TRAPL, 2097TRAPL



Reinventing Safety All Around

The Pass & Seymour® Self-Test GFCI receptacle with SafeLock® Protection conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.

For Hospital Grade, refer to SF708R4.

FEATURES & BENEFITS

Patented SafeLock® Protection: if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

Tamper-resistant automatic shutter system prevents young children from inserting common household objects.

The indicator light flashes if the device fails the self-test, signaling that the GFCI should be replaced.

Side or internal screw-pressure-plate back wire termination with #14 – #10 AWG stranded or solid, copper or copper-clad conductors.

Captive screws make for easier installation.

2097LA

Ground terminal clamp allows for fast installation.

Two back-wire holes per termination add wiring flexibility, eliminate pigtailing and save box space.

Prevents line-load reversal miswire: No power to the face or downstream receptacles if wired incorrectly.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Thinner profile speeds installation by leaving more room for wires in the box.

Auto-ground clip assures a positive ground to metal box.

The most durable GFCI available. Exceeds UL943 voltage surge requirements.

Meets 2015 UL Requirements

FIELD USES/VERTICAL MARKETS

- Industrial
- Retail
- Healthcare
- Office
- Education
- Hospitality/Lodging
- Institutional
- Multiple Dwelling

PASS & SEYMOUR®
Specification Grade Self-Test GFCIs
15 & 20A, 125VAC

ORDERING INFORMATION

Catalog Number	Description	Ratings	Colors	NEMA Config.
Specification Grade Self-Test GFCI Receptacles				
1597TR*	Spec-Grade Tamper-Resistant 15 Amp GFCI	15A 125V	I, W, –, GRY, BK, LA, NI, DB, G	5-15R
1597*	Spec-Grade 15 Amp GFCI	15A 125V	I, W, –, GRY, BK, RED, LA	5-15R
1597TRA*	Audible Alarm Tamper-Resistant GFCI	15A 125V	I, W, –, LA	5-15R
1597SWTTRR*CCD4	Combination Tamper-Resistant Switch/GFCI (No Federal Specification)	15A 125V	I, W, BK, LA	5-15R
1597NTLTR*CC4	Combination Tamper-Resistant 15 Amp Night Light/GFCI	15A 125V	I, W, BK, LA, NI, DB	5-15R
1597TRWR*	Spec-Grade Weather-Resistant 15 Amp GFCI	15A 125V	I, W, –, GRY, BK, LA	5-15R
2097TR*	Spec-Grade Tamper-Resistant 20 Amp GFCI	20A 125V	I, W, –, GRY, BK, RED, LA, NI, DB, G	5-20R
2097*	Spec-Grade 20 Amp GFCI	20A 125V	I, W, –, GRY, BK, RED, LA	5-20R
1597IGTR*	Spec-Grade Isolated Ground Tamper-Resistant GFCI	15A 125V	I, W, O	5-15R
2097IGTR*	Spec-Grade Isolated Ground Tamper-Resistant GFCI	20A 125V	I, W, GRY, O, LA	5-20R
2097NTLTR*	Combination Tamper-Resistant 20 Amp Night Light/GFCI	20A 125V	I, W, GRY, BK, LA	5-20R
2097TRWR*	Spec-Grade Weather-Resistant 20 Amp GFCI	20A 125V	I, W, –, GRY, BK, LA	5-20R
2097TRA*	Spec-Grade Audible Alarm Tamper-Resistant 20 Amp GFCI	20A 125V	I, W, –, LA	5-20R
1597TRNA*	NAFTA-Compliant Spec-Grade Tamper-Resistant GFCI	15A 125V	I, W, GRY, LA	5-15R
2097TRNA*	NAFTA-Compliant Spec-Grade Tamper-Resistant GFCI	20A 125V	I, W, GRY, LA	5-20R
2097NA*	NAFTA-Compliant Spec-Grade 20 Amp GFCI	20A 125V	I, W, GRY, LA, BL	5-20R
1597TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant GFCI	15A 125V	I, W, –, LA	5-15R
2097TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant GFCI	20A 125V	I, W, GRY, LA	5-20R
1597TRSGL	15A Tamper-Resistant Self-Test Simplex GFCI	15A 125V	I, W, GRY, LA, RED, -, BK	5-15R
2097TRSGL	20A Tamper-Resistant Self-Test Simplex GFCI	20A 125V	I, W, GRY, LA, RED, -, BK	5-20R
1597TRAPL	15A Tamper-Resistant Self-Test Sensitive Appliance GFCI	15A 125V	W	5-15R
2097TRAPL	20A Tamper-Resistant Self-Test Sensitive Appliance GFCI	20A 125V	W	5-20R

NEMA 5-15R

NEMA 5-20R

***Color Designation**

I	Ivory	–	Brown	BK	Black	LA	Light Almond
W	White	GRY	Gray	RED	Red	NI	Nickel
G	Graphite	DB	Dark Bronze	O	Orange	BL	Blue

For more information on these and other P&S products refer to our Catalog or visit our web site.

PASS & SEYMOUR®
Specification Grade Self-Test GFCIs
15 & 20A, 125VAC

legrand®

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed File Number E42190, Standard UL498 Attachment Plugs and Receptacles, UL943 GFCIs. Federal Specification WC596, Hospital Grade. Standard CSA C22.2 No. 42 General Use Receptacles, CSA C22.2 No. 144 GFCIs. Conforms to NEMA WD-1 and WD-6.

Performance

Electrical	
Dielectric Voltage	Withstands 1500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 Second Nominal
Frequency	60 Hz
Maximum Working Voltage	125VAC
Voltage Range	102-132VAC
Mechanical	
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG solid or stranded copper conductor only
Product Identification	Ratings are a permanent part of device
Environmental	
Operating Temperature	-35°C to +66°C
Maximum Humidity	95%
Flammability	UL94 V2

Material Specs

Face: Nylon
Body: Nylon
Contacts: .03" Brass (.8)
Mounting Straps: Galvanized Steel
Terminal Screws: Nickel-Plated Steel #8 - 32
Hex Head Grounding Screw: Steel (Green) Flat Head Mounting Screws: Zinc-Plated Steel
Test/Reset Buttons: Nylon
Auto-Ground Clip: Brass Alloy
*Night Light Lens: Lexan®
**Tamper-Resistant Shutter: Thermoplastic

*** For 1597NTLTR and 2097NTLTR Night Light versions only.**
**** For 1597TR and 2097TR Tamper-Resistant versions only.**

Warranty

1 Year

(Note: Depth of 1.03" for Simplex and Appliance versions.)



Dimensions for 15 & 20 Amp

Audible Alarm

Night Light/GFCI

Simplex

Weather-Resistant

Tamper-Resistant

ALSO AVAILABLE...

- USB Charging Devices
- PlugTail® Devices
- Surge Protective & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Night Lights

Electrical Wiring Systems
P.O. Box 4822
Syracuse, NY 13221-4822 Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone:905.738.9195
www.legrand.ca

SF1101R7 — August 2022 – For latest specs visit www.legrand.us/passandseymo © Copyright 2022 All Rights Reserved Legrand EWS/CGXTP