



Double pole, Single Phase AC Manual Motor Controller 30 amp, 600 watts, Suitable as Motor Disconnect

## Features & Benefits

High Horsepower rating of 20HP

Gull-wing shaped brass terminal pressure clamps

Constructed of glass-reinforced thermoplastic

UL508 and cULus Listing of individual device and assembled device within enclosure

Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing

External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|              |                |                   |        |
|--------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Country Of Origin | Mexico |
|--------------|----------------|-------------------|--------|

|          |                       |
|----------|-----------------------|
| Standard | CSA Listed, UL Listed |
|----------|-----------------------|

### Dimensions

|                  |          |                  |          |
|------------------|----------|------------------|----------|
| Product Width US | 1.825 in | Product Depth US | 1.753 in |
|------------------|----------|------------------|----------|

|                   |         |
|-------------------|---------|
| Product Height US | 3.67 in |
|-------------------|---------|

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

---

|                          |                   |                |        |
|--------------------------|-------------------|----------------|--------|
| Operating Cycles         | 50000             | Actuator       | Toggle |
| Connection               | Side & Back Wired | Amperage       | 30 A   |
| Wattage                  | 600 W             | Supply Voltage | 120 V  |
| Environmental Conditions | UL94 V2           |                |        |

---