



**Wiremold**  
**Pop Up Tower, 2 Outlet, 1 USB-A, 1 USB-C**  
Part No. POPUP-BK



The Pop Up Tower allows for convenient access to power and charging while remaining hidden when not in use. The top cap of the tower pops up when pushed in and can be pulled up and locked in the open position, revealing two tamper-resistant outlets, a USB-A port and USB-C port. The USB ports share a combined total output of up to 15W for charging of small electronic devices. When finished with charging, the pop up tower can be pushed back down into the surface once the lock is released at the base of the unit.

## Features & Benefits

**Easy Installation:** Core a hole into furniture to add this pop up outlet and plug the 6 ½ foot cord into a nearby outlet.

**Tamper-Resistant Outlets:** Includes 2 tamper-resistant outlets rated at 15A, 125 VAC.

**USB Charging:** Equipped with 1 USB-A port and 1 USB-C port with a total combined output of 15W at 3.1A.

**Declutter Your Space:** Outlets and USBs stay hidden underneath the surface when unit is not in use and can be brought-up by simply pushing the top cap and pulling the unit up.

## Specifications

### General Info

Product Line	Wiremold	Color	Black
UPC Number	786776194388	Country Of Origin	China
Receptacle Type	5-15R	Number of Receptacles	2

### Dimensions

Product Width US	3.375 in	Product Height US	10.75 in
Cable Length	6.5 ft		

### Listing Agencies / 3rd Party Agencies

ETL Listed	Yes	ETL ListingNumber	5013860
------------	-----	-------------------	---------

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Plug Type	5-15P	Wire Gauge	14 AWG
-----------	-------	------------	--------

---

Is Tamper-Resistant	Yes	Is Pre-Wired	Yes
---------------------	-----	--------------	-----

---

Cord Length	6.5 ft	Number of USBs	2
-------------	--------	----------------	---

---

Amperage	15 A	Current Rating	15 A
----------	------	----------------	------

---

Indoor/Outdoor	Indoor	Cable Size	14 AWG
----------------	--------	------------	--------

---

Maximum Wattage	1875 W	Number of Circuits	1
-----------------	--------	--------------------	---

---

Wiring Method	Cord-ended	NEMA Configuration Code	5-15R
---------------	------------	-------------------------	-------

---

Number of Outlets	2	Voltage	125.0 V
-------------------	---	---------	---------

---

Environmental Conditions	INDOOR
--------------------------	--------

---