

## 150A 600V MALE CAM TYPE PLUG



### Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim bundles wire strands to reduce "splaying."

### Specifications

#### General Info

|                   |                |                    |                       |
|-------------------|----------------|--------------------|-----------------------|
| Product Line      | Pass & Seymour | Color              | Green                 |
| Country Of Origin | Mexico         | Application Sector | Commercial/Industrial |
| Standard          | UL, cCSAus     |                    |                       |

#### Dimensions

|                   |        |
|-------------------|--------|
| Product Length US | 4.3 in |
|-------------------|--------|

#### Technical Information

|           |           |                 |             |
|-----------|-----------|-----------------|-------------|
| Amperage  | 150 A     | Number of Poles | Single Pole |
| Wire Size | 8 - 2 AWG | Voltage         | 600.0 V     |

|                          |  |
|--------------------------|--|
| Environmental Conditions | Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact; Flammability UL94 V2; Enclosure: NEMA Type 3R and 4 |
|--------------------------|--|