




radiant Collection  
radiant® Two-Gang Screwless Wall Plate with Microban®  
Part No. RWP262WAMCC6



This Wall Plate features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

Designed to complement any space, the radiant® Collection features sleek, screwless wall plates for cleaner lines and a sophisticated touch. Pair this two-gang option with your preferred radiant® switch, dimmer, and/or outlet for a completed look that's a step above ordinary.

This product is not currently available for sale in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Adds a touch of sophistication to any space with a sleek, screwless face and low-profile. Sized to fit even over ragged openings for a seamless look.

Designed to exclusively fit the designer switches, dimmers and outlets from the radiant® Collection, snapping into place with ease.

Ensures proper plate positioning with subplate screws.

Molded of highly durable polycarbonate, Wall Plates from the radiant® Collection are available in an array of classic colors and metallic finishes.

## Specifications

### General Info

|              |                          |                    |                        |
|--------------|--------------------------|--------------------|------------------------|
| Product Line | Pass & Seymour           | Country Of Origin  | United States          |
| Features     | Antimicrobial Protection | Application Sector | Residential/Commercial |
| Standard     | RoHS, CSA, UL, cULus     | Type               | Decorator              |

### Dimensions

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 4.96 in | Product Depth US | 0.065 in |
| Product Height US | 4.94 in |                  |          |

### Technical Information

---

|               |          |                          |  |
|---------------|----------|--------------------------|--|
| Thickness     | 0.065 in | Indoor/Outdoor           | Indoor                                       |
| Mounting Type | Box      | Environmental Conditions | 0 to 90% (relative humidity, non-condensing) |

---